

Modec, Inc.

Optional Equipment

Containment Berms. Custom fabricated to the exact dimension required. Air cell berms also available. Produced with heavy-duty chemical resistant materials, these berms can be utilized for vehicle processing as well.



Extenda-pole Scene Lighting. Modec can install high-powered scene lighting on the exterior of the unit. Permanently affixed scene lighting by Whelen is also provided standard. Emergency lighting such as strobes can be added..



Chrome Racking. High quality, hospital grade racking system that can be adjusted. Affords users to tie-down supplies with easy-to-use bungee cords.



Injection Systems. Modec features Dosmatic injection systems for continuous decon solution induction

Decon Stretcher Stanchions. Modec has worked directly with suppliers such as Reeves Manufacturing and NARP in fabricating unique methods of processing ambulatory patients. Decon Stretchers such as the Raven can be utilized more effectively with fold-arm apertures custom fabricated by Modec. Modec has also produced hundreds of **Stainless Steel Decon Tables** that also fold-up and out of the way for maximum operating effectiveness



CAF Systems. Modec routinely installs Decon Foam CAF Systems that feature Ingersoll-Rand Compressors and unique Foam-it delivery devices. These systems can deliver foam decon agents from stations located in various positions inside or outside of the unit. (Unit pictured is 45-gallon system).



Roof Access Ladders. Modec custom produces heavy-duty (non-RV) roof access ladders from high grade steel. Before installation, the ladders are finished in a high quality powder coated paint.




Exterior Operations Panel. Modec can install weather -proof operations panels from which first responders can activate and operate the unit without having to enter the decon unit itself.

Hands-Free Intercoms and Stainless Steel Clothes Chutes. These features can be installed at the customers' request. Our chutes feature all stainless steel construction along with gas spring closing devices.



Grey Water Level High Alarm. We have installed both audio and visual alarm systems to indicate high tank levels of contaminated water. In addition, we have installed solenoids that allow operators to shut-off the alarms at 3/4 full to afford sufficient time to respond to the alarm.



Custom Cabinetry. Modec also produces in-house its own custom cabinets. Featuring high-grade components and hardware, our cabinets can be custom fitted to each unit.



Custom Shower Positions. We can design the interior to accommodate privacy for each showering position. In addition, custom flooring can be implemented to keep run-off isolated to each position.

Curtains can also be installed to provide separation as identified by the customer (i.e. disrobing areas, etc.)



Exterior Decon Operations. Custom fabricated, single-piece modesty protection for exterior decon operations. Features 1-1/4" anodized aluminum tubing that is reinforced for high-wind conditions. Deploys in under 45 seconds and includes sewn in tie down straps. Exterior walls ports and below rail discharge ports also incorporated.



Custom Decaling. Modec can convert any camera-ready art to a full scale, long-lasting vinyl decal application. Our customers can also select from a variety of exterior colors as well.



Exterior Ramp Access. Modec can also provide exterior ramps for its units. Our ramps have means for secure positioning and have safety chains provided.



Negative Air Handling Systems. Modec produces its own negative air handling systems that are normally roof-mounted for easy filter access. Conforming to OSHA standards for air changes per hour and water column pulled, they incorporate HEPA filters and can also be outfitted with UV lights for additional biological efficacy.



Delivery Devices. We can incorporate a variety of delivery devices that are interchangeable at every decon position. This includes drench heads, wands, hoses, brushes and even multiple spray heads units as shown in the picture. Decon solution delivery devices can be incorporated into every decon positioned

